

Machine à laver

Disponibilité : 2

Fabricant : Steelco

Modèle : Lab 640 SL

Année : 2020

Nombreux paniers

Ci-joint le manuel d'instruction à télécharger où vous trouverez le détails (alarmes, options, cycles etc...). Vous pouvez 24 cycles de paramétrages différents (eau, produit, T°, P etc.) avec différentes étapes (évacuation, prélavage, traitement, rinçage, séchage).

- ⇒ 10 cycles de nettoyages sont pré-enregistrés, vous avez le détail pour configurer les cycles.

Pour les paniers, nous disposons :

- Panier 18 positions injecteurs (x2)
- Module de lavage 56 positions (x2)
- Panier de lavage pour pipette (x1)
- Panier de lavage pour verrerie gros volume (x1)
- Panier de lavage 35 positions (x1)

Washing Machine

Availability: 2

Manufacturer: Steelco

Model: Lab 640 SL

Year: 2020

Many baskets

Please find attached the instruction manual, where you will find full details (alarms, options, cycles, etc.). You can set up 24 different cycles (water, detergent, temperature, pressure, etc.) with various stages (drain, pre-wash, treatment, rinse, drying).

- 10 cleaning cycles are pre-programmed; full details are provided for configuring the cycles.

As for the baskets, we have:

- 18-position nozzle basket (x2)
- 56-position washing module (x2)
- Washing basket for pipettes (x1)
- Washing basket for large-volume glassware (x1)
- 35-position washing basket (x1)

Machine à laver



Machine à laver



Machine à laver



Machine à laver



Machine à laver



Machine à laver

